



Analytical HPLC System LD-LAHS-B12

Labodam Equipment Ltd.

info@labodam.com | www.labodam.com

Analytical HPLC System LD-LAHS-B12

Overview

Analytical HPLC System LD-LAHS-B12 is an advanced, highly effective analytical HPLC system with UV-Vis detector with 190 nm to 700 nm wavelength range, and High pressure constant flow pump with the flow range of 0.001 to 10.000 ml/min (step 0.001 ml/min). This HPLC system delivers accurate, reliable results with improved working efficiency. Incorporated with powerful software to control, capture and analyze data, manage the operation.

Features:

- Pumping system: High Pressure Constant Flow Pump
- UV-Vis Detector with 190 nm to 700 nm wavelength range
- Intelligence control of components via workstation
- High pressure constant flow pump with the flow range of 0.001 to 10.000 ml/min
- Delivers accurate, reliable results with improved working efficiency
- Advanced USB chip and optoelectronic isolation ensures stable communication
- Powerful software to control, capture and analyze data, manage the operation
- Real time pressure display, warning for maximum and minimum pressure for security purpose
- Front panel access for quick (parts) replacement without disassembling the instrument

Applications:

Analytical (HPLC) High Performance Liquid Chromatography system has been widely used in Research and Development, Pharmaceutical, Biochemistry, Food Science, Environmental Science for analysis and detection of impurities, ligand-exchange chromatograph, high-pH anion-exchange chromatograph of carbohydrates and oligosaccharide, water purification, pre-concentration of trace components, ion-exchange chromatograph of proteins.

Specifications:

UV-Vis Detector	<table><tr><td>Linear</td><td>2.0 AU</td></tr><tr><td>Wavelength Range</td><td>190 – 700 nm</td></tr><tr><td>Noise</td><td>? ± 0.5, 105 AU</td></tr><tr><td>Drift</td><td>? 1.0 x 10⁴ AU/h</td></tr><tr><td>Cell</td><td>Analytical: Optical Path 10 mm, 11 µL Semi-Prep Scale: Optical Path 2 mm, 6 µL</td></tr><tr><td>Power Supply</td><td>AC 220 V ± 10%, 50 Hz</td></tr><tr><td>Power</td><td>100 W</td></tr><tr><td>Weight</td><td>16 kg</td></tr><tr><td>Dimension (L x W x H)</td><td>420 x 300 x 175 mm</td></tr></table>	Linear	2.0 AU	Wavelength Range	190 – 700 nm	Noise	? ± 0.5, 105 AU	Drift	? 1.0 x 10 ⁴ AU/h	Cell	Analytical: Optical Path 10 mm, 11 µL Semi-Prep Scale: Optical Path 2 mm, 6 µL	Power Supply	AC 220 V ± 10%, 50 Hz	Power	100 W	Weight	16 kg	Dimension (L x W x H)	420 x 300 x 175 mm
Linear	2.0 AU																		
Wavelength Range	190 – 700 nm																		
Noise	? ± 0.5, 105 AU																		
Drift	? 1.0 x 10 ⁴ AU/h																		
Cell	Analytical: Optical Path 10 mm, 11 µL Semi-Prep Scale: Optical Path 2 mm, 6 µL																		
Power Supply	AC 220 V ± 10%, 50 Hz																		
Power	100 W																		
Weight	16 kg																		
Dimension (L x W x H)	420 x 300 x 175 mm																		

Other Parameters	<table> <tr> <td>Solvent Bottle Tray</td><td>01 pc</td></tr> <tr> <td>Sample Injector</td><td>Rheodyne 01 pc</td></tr> <tr> <td>Column</td><td>Supersil ODS2 5 µm</td></tr> <tr> <td>Workstation</td><td>Advance Control Sytem</td></tr> <tr> <td>Mounting Frame</td><td>Yes</td></tr> <tr> <td>Degasser</td><td>Optional</td></tr> <tr> <td>System Kit</td><td>Yes (e.g. wrench, screwdriver, pipe etc.)</td></tr> <tr> <td>Power Supply</td><td>AC 220 V ± 10%, 50 Hz</td></tr> <tr> <td>Weight</td><td>45 kg</td></tr> <tr> <td>Dimension (L x W x H)</td><td>600 x 440 x 380 mm</td></tr> </table>	Solvent Bottle Tray	01 pc	Sample Injector	Rheodyne 01 pc	Column	Supersil ODS2 5 µm	Workstation	Advance Control Sytem	Mounting Frame	Yes	Degasser	Optional	System Kit	Yes (e.g. wrench, screwdriver, pipe etc.)	Power Supply	AC 220 V ± 10%, 50 Hz	Weight	45 kg	Dimension (L x W x H)	600 x 440 x 380 mm
Solvent Bottle Tray	01 pc																				
Sample Injector	Rheodyne 01 pc																				
Column	Supersil ODS2 5 µm																				
Workstation	Advance Control Sytem																				
Mounting Frame	Yes																				
Degasser	Optional																				
System Kit	Yes (e.g. wrench, screwdriver, pipe etc.)																				
Power Supply	AC 220 V ± 10%, 50 Hz																				
Weight	45 kg																				
Dimension (L x W x H)	600 x 440 x 380 mm																				
High Pressure Constant Flow Pump	<table> <tr> <td>Flow Range</td><td>0.001 to 10.000 ml/min (step 0.001 ml/min)</td></tr> <tr> <td>Accuracy</td><td>? ± 0.2%</td></tr> <tr> <td>Precision</td><td>? 0.06% RSD</td></tr> <tr> <td>Pressure Range</td><td>0 – 45 MPa</td></tr> <tr> <td>Power Supply</td><td>AC 220 V ± 10%, 50 Hz</td></tr> <tr> <td>Power</td><td>80 W</td></tr> <tr> <td>Weight</td><td>12 kg</td></tr> <tr> <td>Dimension (L x W x H)</td><td>400 x 300 x 180 mm</td></tr> </table>	Flow Range	0.001 to 10.000 ml/min (step 0.001 ml/min)	Accuracy	? ± 0.2%	Precision	? 0.06% RSD	Pressure Range	0 – 45 MPa	Power Supply	AC 220 V ± 10%, 50 Hz	Power	80 W	Weight	12 kg	Dimension (L x W x H)	400 x 300 x 180 mm				
Flow Range	0.001 to 10.000 ml/min (step 0.001 ml/min)																				
Accuracy	? ± 0.2%																				
Precision	? 0.06% RSD																				
Pressure Range	0 – 45 MPa																				
Power Supply	AC 220 V ± 10%, 50 Hz																				
Power	80 W																				
Weight	12 kg																				
Dimension (L x W x H)	400 x 300 x 180 mm																				