



Mute Ultrasonic Cleaner LD-LMC-A16

Labodam Equipment Ltd.

info@labodam.com | www.labodam.com

Mute Ultrasonic Cleaner LD-LMC-A16

Overview

Mute Ultrasonic Cleaner LD-LMC-A16 is a compact and robust 22.5 L tanked structure that creates waves in the tank water to clean glassware and instruments from grime. LCD screen provides a clear and detailed display of many data such as temperature, voltage, current, and malfunction. It also shows the instrument type, ultrasonic power, frequency, and time, alarm that beeps. Premium 304 stainless steel plate is used to make the instrument's inner groove. Capable of adjusting the power exerted, the ultrasonic cleaner also protects fragile equipment. Equipped with degassing and degreasing function for removal of dissolved gasses and cleansing of the tank.

Features:

- 22.5 L capacity tank
- Integrated digital circuit for timer and heater
- Temperature range : RT ~ 80 °C
- Cleaning duration : 1 ~ 9999 mins
- Specialized degassing technology for quick degassing and productive work
- Distinctive Sweep technique for consistent ultrasonic dispersion and automated frequency tracking
- The instrument mute design uses premium sound-absorbing materials to reduce operating noise to less than 60 dB
- To make carrying and transporting the instrument easier, a handle is fitted on both sides

Applications:

Ideal for cleaning lenses and other optical parts, dental and surgical instruments, electronics, tools, pens, firearms, jewelry, and golf clubs. It is also used in manufacturing and maintenance of aerospace, engineering, filtration, orthopedic implants, pharmaceutical, plating and surface finishing, printing technology and equipment etc.

Specifications:

Capacity	22.5 L
Grid Cover	Yes
Heating Power	1000 W
Time Adjustable	1 – 9999 mins
Power Adjustable	10 – 100%
Ultrasonic Power	600 W
Ultrasound Frequency	40 kHz
Tank size (L x W x H)	500 x 300 x 150 mm
Temperature Adjustable	RT – 80 °C

Machine size (L x W x H)	530 x 320 x 385 mm
---------------------------------	--------------------